



Drawings not to scale
All dimensions in mm

SPECIFICATION

CONTACT FORM / STYLE		Normally Open
SWITCHING VOLTAGE	Max. Vac RMS	60
SWITCHING CURRENT	Max. A	0.25
SWITCHING CAPACITY	Max. VA	3
OPERATING ANGLE	Deg.°	60° ± 10°
CONTACT RESISTANCE	Max. mΩ	5
OPERATING TEMPERATURE	Deg. °C	-37° +10°
STORAGE TEMPERATURE	Deg. °C	-40° +125°
CASE MATERIAL		Steel Tin Plated
CABLE / TERMINATION		1 Pin

TIP-OVER SWITCH - Mercury Free

PART NUMBER
CW1260-0

Rev. No.	Revision Note	Date	Signature
A	Web Site 1999	1-5-99	RG

The Comus Group of Companies consist of:
Assemtch Europe Limited
E. Bachem GmbH
Comus International
W. Gunther GmbH
Gunther Belgium
Gunther France
S.T.G.

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.