


## PCB - PTF 0,3/ 4-FLEX-L-8 - 1848480

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Accessories, Number of positions: 4, Pitch: 1.9 mm, Mounting: PCB connector




### Why buy this product

- Corner connection for implementing complex arrangements of flexible LED printed-circuit boards
- Easy connection of flexible LED printed-circuit boards
- Minimal heating during operation
- UL-approved materials



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 20 pc   |
| Minimum order quantity               | 20 pc   |
| GTIN                                 | <br>4 055626 282213 |
| Weight per Piece (excluding packing) | 0.21 g  |
| Country of origin                    | Netherlands   |

### Technical data

|                     |                      |
|---------------------|----------------------|
| Product type        | PCB plug             |
| Number of positions | 4                    |
| Pitch               | 1.9 mm               |
| Plug-in system      | COMBICON COMPACT PTF |
| Product family      | PTF 0,3/...-Flex     |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.1 | 27141190 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 8.0 | 27440490 |

# PCB - PTF 0,3/ 4-FLEX-L-8 - 1848480

## Classifications

ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC002643 |
| ETIM 5.0 | EC002637 |

## Accessories

### Additional products

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H - 1707558



Plug component, Nominal current: 10 A, Rated voltage (III/2): 24 V, Number of positions: 2, Pitch: 1.9 mm, Color: white, Contact surface: Tin, Mounting: Direct plug-in method, Length of the punched-on cables: 500 mm for flexible PCBs with a width of 8 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

Printed-circuit board connector - PTF 0,3/ 4-BB-8-H - 1707559



Plug component, Nominal current: 10 A, Rated voltage (III/2): 24 V, Number of positions: 4, Pitch: 1.9 mm, Color: white, Contact surface: Tin, Mounting: Direct plug-in method, for flexible PCBs with a width of 8 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

Printed-circuit board connector - PTF 0,3/ 4-WB-8-H - 1707561



Plug component, Nominal current: 10 A, Rated voltage (III/2): 24 V, Number of positions: 4, Pitch: 1.9 mm, Color: white, Contact surface: Tin, Mounting: Direct plug-in method, Length of the punched-on cables: 500 mm for flexible PCBs with a width of 8 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

## Drawings

Dimensional drawing

