


JWPF Waterproof Connector



Compact waterproof wire to wire / wire to Board connector system

- Housing Lock for secure mating
- Double Leaf Contact Construction

- IP67 Rating

Current Rating	3.0A AC DC	Plating	Tin
Pitch	2mm	Housing	Nylon
Voltage	100V AC DC	Applicable Wire	AWG 26 to 22
Contacts	Phosphor Bronze - Female		OD 1.4mm to 1.74mm
	Brass - Male	Temperature Range	-25°C to +85°C

454720

Order Multiple=5		Price Each
No of WaysMftrs. List No.	Order Code	
Receptacle Housing Assembly		
2	02R-JWPF-VSLE-S	384-9806 ●
3	03R-JWPF-VSLE-S	384-9820 ●
4	04R-JWPF-VSLE-S	384-9843 ●
Tab Housing Assembly		
2	02T-JWPF-VSLE-S	384-9818 ●
3	03T-JWPF-VSLE-S	384-9831 ●
4	04T-JWPF-VSLE-S	384-9855 ●
PCB Header		
2	B02B-JWPF-SK-R(LF)(SN)	132-4125 ●
3	B03B-JWPF-SK-R(LF)(SN)	132-4126 ●
4	B04B-JWPF-SK-R(LF)(SN)	132-4127 ●
Order Multiple=10		Price Each
Contacts for JWPF		
Socket	SWPR-001T-P025	384-9788 ●
Tab	SWPT-001T-025	384-9790 ●
		Price Each
Crimp Tool	WC-JWPF	434-1430 ●
Extraction Tool	EJ-JWPF	434-1442 ●