

## Profile Deep Wide Surface 30

Profile Deep Wide Surface 30 CDE-9/T 2m anodised  
0022599



### Product features

- A deep wide 1000mm length anodised aluminium lighting profile that can be combined with multiple click diffusers (flat opal - 0022620, round opal - 0022621, square opal - 0022630) with a maximum LED strip width of 20mm. Can be mounted with 'Profile HO surface 16 raw alu.' or dedicated plates. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



## PRODUCT OVERVIEW

Product name	Profile Deep Wide Surface 30 CDE-9/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288225999

## DATA TABLE

### General data

Product name	Profile Deep Wide Surface 30 CDE-9/T 2m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
Warranty	3 years

### Physical data

Housing colour	Silver
Nominal Product Length (mm)	2000
Nominal Product Width (mm)	33.4
Nominal Product Height (mm)	29.6
Weight (kg)	0.722

### Packaging

Single packaging type	Carton
Product EAN number	5410288225999
Packaging single length / height (cm)	200.0
Packaging single width (cm)	3.0
Packaging single depth (cm)	2.0

## Profile Deep Wide Surface 30

*Profile Deep Wide Surface 30 CDE-9/T 2m anodised*

0022599

DUN14 (outer)	05410288225999
Units per outer package	20
Packaging outer length / height (cm)	211.2
Packaging outer width (cm)	17.3
Packaging outer depth (cm)	17.5

### TECHNICAL DRAWINGS

