

Panel trucks with rubberised strip
with 2 support rollers, load-bearing capacity 400 kg

Application:

For transporting panels, sheets and other large parts.

Execution:

- Steel tube construction with steel sheet toe plate
- For longitudinal transportation of large area wood and plastic panels
- Total width 680 mm
- Wheels with plastic rims and roller bearings
- 2 support rollers 50 mm diameter
- Surfaces coated in profile rubber (non-slip) and adjustable hold-down device as tilt protection
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant

Advantage:

- Practical hold-down clamp for tilt protection

Delivery:

Disassembled



Art. no.	50270 363
Brand	FETRA
Manufacturer Part Number	2076
Height	1460 mm
Material of wheel	Air
Load-carrying capacity	350 kg
Wheel diameter	260 mm
Wheel width	85 mm
Width	680 mm
Toe plate width	200 mm
Toe plate depth	500 mm
Total stop optional	No
Gross Weight	18.000 kg
Product Group	5AB

EAN

4017976020761