

MODLINK MSDD DATA INSERT

2xUSB-A female/female + 1xRJ45

RJ45; USB; USB (A)
 1 × RJ45, 8-pole metal, CAT5e (female/female)
 2 × USB (female/female) form A

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037785
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	60 mm

Environmental characteristics | Climatic

Storage temperature min.	-20 °C
Storage temperature max.	60 °C

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque 0,9 Nm

USB

Operating voltage AC 48 V

Operating voltage DC 48 V

Operating voltage DC (UL-listed) 42,4 V

Operating current max. 500 mA

USB specification 2.0

Data transmission rate max. 480 MBit/s

Looking techniques Snap-in connector

RJ45

Operating voltage AC max. (UL-listed) 30 V

Operating voltage DC max. (UL-listed) 42,4 V

Current operating max. (UL) 175 mA

Family construction form RJ45

Family type Back side RJ45

Cable category min. Cat5e

Looking techniques Snap-in connector