



OPTIONS



VERSIONS

Type	Rated Power W	Rated Torque Ncm	Rated Current A	Rated Voltage V	Rated Speed rpm	Torque Constant Ncm/A	Rotor Inertia gcm ²	Weight kg	Length „A“ mm
DB59S024035	84	23	5	24	3500	4.5	75	0.52	53.6 mm - 54 mm
DB59M024035	135	37	8	24	3500	4.6	105	0.65	53.6 mm - 54 mm
DB59L024035	172	47	9.4	24	3500	5	119	0.72	53.6 mm - 73.6 mm
DB59C024035	220	60	13.6	24	3500	4.4	173	0.95	53.6 mm - 93.6 mm

ORDER IDENTIFIER



DB59S024035-

A* = single shaft

* also available for individual configuration with encoder and brake on our website

ACCESSORIES



ZD-DF56

Damper

DIMENSIONS (IN MM)

DB59

