

Product information

13 46 165

Stripping Pliers

IEC 60900 DIN EN 60900



⚡ 1000 V 



Versatile and comfortable: a true all-rounder in electrics

- Multifunctional - cutting and stripping with one pair of pliers
- For time-saving stripping of all round sheathed and damp-proof installation cables (e.g. NYM cable)
- Simplified access especially into deep mounted junction boxes thanks to slim head design and optimally angled cable sheath cutter
- Strip cables easily and without damage thanks to circular cutting edge with depth limiter
- Suitable for universal use: precision wire stripping holes for conductors from 1.5 and 2.5 mm²
- With side cutters for cutting and trimming conductors, wires, small screws and nails
- All cutters additionally induction-hardened to approx. 61 HRC for high wear resistance
- 30 % lighter than comparable pliers
- Vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	13 46 165
EAN	4003773079699
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	190 g
Dimensions	165 x 57 x 27 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 3.2 mm
Cutting capacities hard wire (diameter)	Ø 2.2 mm
Cable stripping values (diameter)	8 – 13 mm
Stripping capacities in square millimetres	0.75 — 1.5 mm ² / 2.5 mm ²
VDE tested	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510

technical change and errors excepted

