

## Inset Trend 75 Square IP44

INSET TR SW SQ IP44 INDOOR BLK EX-LMP  
3084103



### Product features

- INSET TREND SQ SW BK EX-LMP



## PRODUCT OVERVIEW

Product name	INSET TR SW SQ IP44 INDOOR BLK EX-LMP
Technology	LED/Halogen
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Museums & Galleries, Retail
ETIM Class	N/A
E-number FI	4225702
Warranty	3 years
Photobiological Risk Group	Not applicable
Electrical protection	Class II
Housing colour	RAL 9004 - Signal black
IP rating	IP44/20
IK rating	IK02
Product EAN number	8711971841036

## DATA TABLE

### General data

Product name	INSET TR SW SQ IP44 INDOOR BLK EX-LMP
Technology	LED/Halogen
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Museums & Galleries, Retail
ETIM Class	N/A
E-number FI	4225702
Warranty	3 years

### Optical data

Photobiological Risk Group	Not applicable
----------------------------	----------------

### Electrical data

Mains voltage (V)	220-240V
Electrical protection	Class II
Control gear required	No

## Inset Trend 75 Square IP44

*INSET TR SW SQ IP44 INDOOR BLK EX-LMP*  
3084103

Transformer required	No
Glow Wire Test (°C)	650

### Physical data

Housing colour	RAL 9004 - Signal black
IP rating	IP44/20
IK rating	IK02
Nominal Product Length (mm)	95
Nominal Product Width (mm)	95
Nominal Product Height (mm)	100
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.18
Recessed Depth (mm)	115

### Packaging

Single packaging type	Carton
Product EAN number	8711971841036
Packaging single length / height (cm)	13.0
Packaging single width (cm)	10.0
Packaging single depth (cm)	8.5
DUN14 (outer)	18711971841033
Units per outer package	30
Packaging outer length / height (cm)	53.0
Packaging outer width (cm)	49.0
Packaging outer depth (cm)	22.0

## TECHNICAL DRAWINGS

