

STELVIO 30266-01LA



S3 SRC - WR HRO CI HI - UNI EN ISO 20345:2012

UPPER

Water repellent and breathable 2.2mm grain leather. Anti abrasion leather toe cap and heel part. Collar in full grain calf leather.

LINING

Calf leather + textile with TE-POR waterproof membrane combined with WIN-THERM thermal insulator that guarantees dry comfort even at a temperature of -30°C

INSOLE

Ergonomic, in removable felt with aluminium insert for exceptional thermal insulation suitable for low temperatures.

SOLE

New generation polyurethane-rubber. Expanded EXTRA LIGHT polyurethane midsole, guarantees both total comfort and shock absorption on any kind of surface. Anti-static, SUPER GRIP rubber outsole, resistant to a contact heat of up to 300°, slip resistance characteristics at the highest levels, resistant to corrosion by oils and hydrocarbons. Non marking outsole!

TOE CAP

Composite POWER CAP, ultra-lightweight, undetectable by metal detectors, shock absorption max, 200 Joules, Exclusive toe cap produced in fiberglass, kevlar and rubber to guarantee a higher elastic memory and perfect thermal insulation.

MIDSOLE

Multi layer composite WITH ZERO PERFORATION. Extremely flexible, lightweight, imperceptible during walking. Moreover, it guarantees perfect thermal insulation.

SIZES FITTING WEIGHT SIZE 42 38-48 MONDOPOINT 11 740 gms - half pair





















Shock absorbent

Oil and fuel

Antistatic shoe

Heat resistant sole

Steel or composite

Breathable upper

Water-repellent

Steel or composite

Insulation from cold

PANTHER S.r.I. via E.Berto, 2 BOVOLENTA 35024 Padova, Italy - T +39 049 9713211 - F +39 049 5806906 - info@panthersafety.it