

Torque interchangeable blades.



2859 Torque TORX® interchangeable blade.
For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: dark green.

Application: For applications where recommended torque settings are important.
Extra: Very slim blade diameter for hard-to-reach screws.

Order-No.	●	●	↔	↔	max. Nm	↔
30852	T4	4	175	42	0.25	10
26158	T5	4	175	42	0.4	10
26064	T6	4	175	42	0.6	10
26065	T7	4	175	42	0.9	10
26066	T8	4	175	42	1.3	10
26059	T9	4	175	42	2.5	10
26067	T10	4	175	42	3.7	10
26068	T15	4	175	42	5.5	10
26069	T20	4	175	42	8.0	10
26070	T25	4	175	42	8.0	10

Torque interchangeable blades.



2859 Torque TORX PLUS® interchangeable blade.
For Wiha torque screwdrivers.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: light green.

Application: For applications where recommended torque settings are important.
Extra: Very slim blade diameter for hard-to-reach screws.

Order-No.	●	●	↔	↔	max. Nm	↔
26159	5IP	4	175	42	0.5	10
26071	6IP	4	175	42	0.8	10
26152	7IP	4	175	42	1.3	10
26072	8IP	4	175	42	2.0	10
26154	9IP	4	175	42	3.0	10
26155	10IP	4	175	42	4.5	10
26073	15IP	4	175	42	6.6	10
26156	20IP	4	175	42	8.0	10
26157	25IP	4	175	42	8.0	10



2859 Torque TORX® MagicSpring® interchangeable blade.
For Wiha torque screwdrivers.
Retaining spring holds TORX® screws in place.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: dark green.

Application: For applications where recommended torque settings are important.
Extra: Very slim blade diameter for hard-to-reach screws.

Order-No.	●	●	↔	↔	max. Nm	↔
27818	T6	4	175	42	0.6	10
27812	T7	4	175	42	0.9	10
27813	T8	4	175	42	1.3	10
27814	T9	4	175	42	2.5	10
27815	T10	4	175	42	3.8	10
27816	T15	4	175	42	5.5	10
27817	T20	4	175	42	8.0	10
29467	T25	4	175	42	8.0	10



2859 Torque TORX PLUS® MagicSpring® interchangeable blade.
For Wiha torque screwdrivers.
Retaining spring holds TORX PLUS® screws in place.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Colour-coding: light green.

Application: For applications where recommended torque settings are important.
Extra: Very slim blade diameter for hard-to-reach screws.

Order-No.	●	●	↔	↔	max. Nm	↔
29553	6IP	4	175	42	0.8	10
29554	7IP	4	175	42	1.3	10
29555	8IP	4	175	42	2.0	10
29556	9IP	4	175	42	3.0	10
29557	10IP	4	175	42	4.5	10
29558	15IP	4	175	42	6.6	10
29559	20IP	4	175	42	8.0	10
29560	25IP	4	175	42	8.0	10



2859 Torque bit universal holder.
For Wiha torque screwdrivers.
Suitable for C 6.3 and E 6.3 (1/4") bits.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Sleeve: Made of stainless steel, black-plastic coated.

Application: For applications where recommended torque settings are important.

Order-No.	○	●	↔	↔	↔
27526	1/4	4	162	11	10



2859 Torque adapter blade.
For Wiha torque screwdrivers.
Suitable for 1/4" square sockets.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Head: Nickel-plated, spring-mounted ball.

Application: For applications where recommended torque settings are important.

Order-No.	●	●	↔	↔	↔
26229	1/4	4	155		10