

## Han-Quintax module, female



Part number	09 14 002 3101
Specification	Han-Quintax module, female
HARTING eCatalogue	<a href="https://b2b.harting.com/09140023101">https://b2b.harting.com/09140023101</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han-Quintax® module

### Version

Termination method	Crimp termination
Gender	Female

### Technical characteristics

Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$

### Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076



Pushing Performance

## Specifications and approvals

CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	2
Net weight	14.4 g
Country of origin	Germany
Customs tariff number	85389099