

# 2J664B

## Specification:

Frequency	AMPS (824-894 MHz)/ISM (868 MHz)/GSM (900 MHz) DCS (1800 MHz)/PCS (1900 MHz)/3G (UMTS 2.1 GHz) WIFI / BLUETOOTH (2.4 GHz)
Impedance	50 Ohms
Polarization	Linear
Gain	2.2 dBi
VSWR	<2:1
Operating temperature	-40°C to +85°C

## Connection:

Connector type	upon request
Cable length	upon request
Cable type	RG174U

## Dimensions:

Max diameter	76mm
Max height	16mm
Nut size	M14
Screw diameter	M14
Screw length	16mm

## Housing:

Color	Black
Material	ABS

