




ADOGH040ZDS0002H04

Connection technology





Product characteristics

Socket	
M12 connector	
Power cable	
T-coded	
Gold-plated contacts	
Electrical data	
Electrical design	AC
Operating voltage [V]	60 AC
Current rating [A]	12
Environment	
Ambient temperature [°C]	-25...85
Protection	IP 67
Mechanical data	
Design	straight
Material body	TPU
Material nut	diecast zinc; nickel-plated
Weight [kg]	0.239
Electrical connection	
Connection	PUR cable / 2 m; 4 x 1.5 mm ² ; Ø 8 mm; Gold-plated contacts
Sheath colour	black

Wiring

Core colours

- BK black
- BN brown
- BU blue
- WH white



Remarks

Pack quantity	[piece]	1
---------------	---------	---