

MOUNTING FRAME FOR KTP 1000 BASIC, MP 277 10" TOUCH, MP 377 12" TOUCH, THIN CLIENT 10", IP65 AND SHEET THICKNESS < 2 MM



Product type designation	
Installation type/mounting	
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	90 %
Mechanics/material	
Type of housing (front)	
• Sheet metal	Yes
Scope of supply	
Delivery unit in items	1
other	
Note:	For KTP1000 Basic, MP 277 10" Touch, MP 377 12" Touch, Thin Client 10"

Usable in the following products

- Product 1
- Product 2
- Product 3
- Product 4
- Product 5

[6AV6647-0AE11-3AX0](#)

[6AV6647-0AF11-3AX0](#)

[6AV6643-0CD01-1AX0](#)

[6AV6643-7CD00-0CJ0](#)

[6AV6643-7CD00-0CJ1](#)

last modified:

12.03.2015