


CONSUMER ITEM	LENGTH (mm)
PSG3328-HDMI-10M	10000±100
PSG3329-HDMI-15M	15000±100
PSG3330-HDMI-20M	20000±100

1. 100% OPEN SHORT MIS WIRE TEST
2. CONTACT RESISTANCE:5 OHM MAX
3. INSULATION RESISTANCE:5M OHM MIN
4. HI-POT TEST:DC 300V/10ms
5. PASS 4K@60HZ/4:4:4 / 18Gbps EST

CONSUMER ITEM	LENGTH (mm)
PSG3331-HDMI-25M	25000±100
PSG3332-HDMI-30M	30000±100
PSG3333-HDMI-40M	40000±100
PSG3334-HDMI-50M	50000±100

HDMI AM Gold plated

HDMI AM Gold plated



由 Autodesk 教育版产品制作

HDMI	Signal Assignment	HDMI
1 Red	Red	1 Red
2 Blue	Blue	2 Blue
3 Green	Green	3 Green
4 Brown	Brown	4 Brown
5 Black	Black	5 Black
6 White	White	6 White
7 Yellow	Yellow	7 Yellow
13 Green	CEC	13 Green
14 Orange	Orange	14 Orange
19 Purple	Purple	19 Purple
18 Red	+5 Volts Power	18 Red

APPROVED	CHECKED	DRAWING	DESIGNED	DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	IRD ANGLE
				MODEL NO.		△			
				DRAWING NO.	256-051	△			
				FINISHING		△	2020/6/23		A1
				MATERIAL		SYM	DATE		REVISION

L.W.H

QR-025 2007.05.03, A1