

Clamps



Version:

- Heat-treated steel
- Painted
- With self-locking trapezoidal thread spindle and end safety device.
- With flat support

Art. no.	26157 060
Min./max. support plate height	140-210 mm
Diameter	80 mm
Head diameter	70 mm
Max. force range	170 kN
Centring diameter	12 mm

EAN-Code

4020772072438

