

Data logger for temperature

ORION[®]

Application:

For environmental monitoring, e.g. during transportation and storage

Execution:

- Large display for current value indication and
- External temperature sensor connection
- Battery status indication
- User-friendly Windows software
- Hi-Lo visual and acoustic alarm
- Memory for up to 60,000 measured values with 3 variables
- Measuring interval adjustable from 1 second up to 24 hours
- High accuracy: $\pm 0.5^{\circ}\text{C}/\pm 3\%$

Delivery:

USB data cable, Windows software on CD and battery (1x 3 V lithium type CR2032)



Art. no.	46200 010
Brand	ORION
Manufacturer Part Number	46200010
Min./max. temperature measuring range	-30 to 70 °C
Digit increment (measuring instrument for temperature)	0.1 °C
Temperature error limit	0.5 °C
Temperature error limit (residual area)	0.7 °C
IP protection class	IP 65
Gross Weight	0.144 kg
Product Group	456

EAN

4039247962198