

## Workbench with electric height adjustment

Solid beechwood 1500 mm, height-adjustable via key panel

### Application:

For standing activities.

### Execution:

- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, central horizontal strut, with level compensation on all four feet
- Height infinitely adjustable from approx. 740-1040 mm via an electric control panel
- Bevel gears with hardened steel gear wheels
- Gear housing made of die-cast zinc
- One perforated metal panel wall on both the right and left end faces of the workbench
- Delivered fully assembled

### Advantage:

- The workbench can quickly and easily be adjusted to the desired working height
- For perfect ergonomics in the workplace
- Up to 4 different work heights are programmable and accessible at the touch of a button thanks to the memory function
- When you buy this product, you plant a tree and also receive a tree certificate!



<b>Art. no.</b>	<b>50185 014</b>
<b>Levelling</b>	Yes
<b>Worktop width</b>	1500 mm
<b>Adjustable in height</b>	Yes
<b>Material of frame</b>	Steel plate
<b>Worktop height</b>	50 mm
<b>Max. height adjustment</b>	1040 mm
<b>Worktop depth</b>	700 mm
<b>Min. height adjustment</b>	740 mm
<b>Surface</b>	Powder-coated
<b>Load-carrying capacity</b>	800 kg
<b>Dynamic load-carrying capacity</b>	400 kg
<b>Material of worktop</b>	Solid beech
<b>Product Group</b>	Prod. Gr. 5BC

### EAN

4053625082339