

Folding trolley

Complete with one folding box

CLAX

Application:

Picking trolley, lab trolley, shopping trolley, shelf trolley, serving trolley, post handling trolley, folding trolley for field service.

Execution:

- Load-bearing capacity, upper shelf: 20 kg
- Load-bearing capacity, lower shelf: 40 kg
- Front wheel diameter: 90 mm, rear: 170 mm
- Durable plastic-aluminium construction
- Platform trolley with 2 levels

Advantage:

- Easy to unfold and fold up in just 2 seconds, using only a single button
- Transport standard folding boxes, drink crates and much more
- Locking brake for safe loading and unloading
- Tensioning belt for securing the folding box to the upper shelf
- Secure footing when closed thanks to the support stands



Art. no.	50392 034
Brand	CLAX
Manufacturer Part Number	0040002-4
Load-carrying capacity	60 kg
Length	910 mm
Width	550 mm
Height	1030 mm
Loading surface length	505 mm
Loading surface size	505 x 355 mm
Loading-surface width	355 mm
Material of loading surface	Plastic
Colour	Pink
Number of steering rollers	2
Number of fixed rollers	2
With wheel lock	Yes
ESD-capable	No
Material of wheel	Solid rubber
Made in	Germany
Number of loading surfaces	2
Gross Weight	8.600 kg
Product Group	559

EAN

4260384780097