

## DULUX S BL UVA 9 W/78

OSRAM BLUE | Lamps



### Areas of application

- Polymerization of blue-sensitive plastics, adhesives, paints and dyes (BLUE)
- Curing plastics (BLUE UVA)
- Sealing surfaces in dentistry (BLUE UVA)
- Cosmetic finger nail treatments (BLUE UVA)
- Insect traps (BLUE UVA)
- Exposure during printed circuit board manufacturing (BLUE UVA)
- Terrariums (BLUE UVA)
- Scientific investigations (BLUE UVA)



# Product datasheet

## Technical data


### Electrical data

Nominal wattage	9.00 W
Lamp voltage	60 V
Lamp current	0.18 A

### Photometrical data

Radiated power 315...400 nm (UVA)	1.5 W
-----------------------------------	-------

### Dimensions & weight



Diameter	12.0 mm
Length	165.5 mm

### Additional product data

Base (standard designation)	G23
-----------------------------	-----

## Product datasheet

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899125094	DULUX S BL UVA 9 W/78	Folding carton box 1	- x - x -		
4052899125100	DULUX S BL UVA 9 W/78	Shipping carton box 10	126 mm x 81 mm x 183 mm	1.87 dm <sup>3</sup>	451.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.