U.I. Lapp GmbH PRODUCT INFORMATION & LAPP GROUP SKINMATIC® RZ 07.11.2014

Adjustable for all wrench sizes ranging from 14 to 33 mm Assembling after the cables are already inserted Ergonomic plastic grips



Assembly time



Space requirement

Application range

For quick mounting of cable and conduit glands Suitable for polyamide and brass cable glands

Product features

Made of chromium-plated tool steel
With two expandable clamping ranges (lock positions)

Small opening (14 - 22 mm): M12 to M16, PG7 to PG11, NPT 3/8"

Large opening (24 - 33 mm): M20 to M25, PG13.5 to PG21, NPT 1/2" to 3/4"

Remark

Not subjected to RoHS directive. Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Classification: ETIM 5.0 Class-ID: EC002132

ETIM 5.0 Class-Description: momentum wrench



Document: LA
LATT_TRO1063EN.p
=N.pdf

2/2

Product Management

Part number	Article designation / size	Width of flat surface (mm)	Overall length (mm)	Pieces / PU
SKINMATIC® RZ				
61791260	SKINMATIC® RZ	14 - 33	250.0	1

07:11:2014		
	SKINMATIC® RZ	
LIP CADE		GmbH
	DRODI IOT INEODMATION	U.I. Lapp