

HEAT EXCHANGER;36W PER K AIR AIR SPEC.
THERMINAL CAPACITY. 36W PER K 316X771X93 MM
(WXHXD) DEGREE OF PROTECTION IP 54

Model		
product brand name		SIVACON
Product designation		air-air heat exchanger
Design of the temperature control		without thermostat

Main circuit		
Operating voltage		
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230

Product details		
Product component		
• Heating		No
• Thermostat		No

Mechanical Design		
Height	mm	771
Width	mm	316
Depth	mm	93
Installation location		Control cabinet...panels, door

Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		E
• acc. to DIN EN 81346-2		E

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64235ML36>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR64235ML36/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR64235ML36

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015