

## Han Domino Pneumatic cube (MF.2)




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 931 2001
Specification	Han Domino Pneumatic cube (MF.2)
HARTING eCatalogue	<a href="https://b2b.harting.com/09149312001">https://b2b.harting.com/09149312001</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Domino Pneumatic Cube
Size of the module	Domino module
Description of the module	Large Tab

### Version

Gender	Male Female
Number of contacts	1
Details	Please order contacts separately.

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥10,000

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	2
Net weight	0.004 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140185302
eCl@ss	27440220 Module for industrial connectors (pneumatic)