



6600Z/288 R

- snaps into T-shape when open so that all key hooks are equally accessible
- both halves of the cabinet can be opened individually - each half is secured with a lock
- extremely robust construction
- numbered, adjustable key strips
- hook heads secured with red plastic caps
- neutral paper strip on the back, removable for individual labelling
- R = standard version, door handed right
- L = special version, door handed left, no surcharge
- W = only for cylinder key, smaller spacing of the hook strips
- key register
- light grey (RAL 7035)
- hook spacing: 30 mm

ExternalKey: 4003482068304

Basic data

Article no. 6600 Z/288 R

Material no. SAP 6830

Main material

Incl. fixing material yes

Cylinder Zyl. 52

Dimensions and weights

Product outer height	550,00 mm
----------------------	-----------

Product outer width	385,00 mm
---------------------	-----------

Product outer depth	160,00 mm
---------------------	-----------

Product net weight	17,150 kg
--------------------	-----------

Distance hooks (right/left)	30.00 mm
-----------------------------	----------

Product features

Number of key hooks	288.00 Stk
---------------------	------------

Number of folding/sliding panels	4.00 Stk
----------------------------------	----------

Prepared for profile cylinder	no
-------------------------------	----

Variants

Article no.	Article abstract
6600 Z/288 R	key cabinets 6600 Z/288 R
6600 Z/288 L	key cabinets 6600 Z/288 L
6600/240 R	key cabinets 6600/240 R
6600/240 L	key cabinets 6600/240 L
