

Stamped crimp contacts



Identification	Wire gauge (mm <sup>2</sup> )	Part No.		
----------------	-------------------------------	----------	--	--

D-Sub

Performance levels  
 Explanations see page 05.04  
 Other performance levels on request



stamped female contacts

Performance level 3

Performance level 2

Performance level 1

Individual contacts

AWG 28-24  
 0.09-0.25  
 stranded

09 67 000 7277<sup>1)</sup>

09 67 000 7278<sup>1)</sup>

09 67 000 7276<sup>1)</sup>

500 pieces/reel  
 Unrolling left

09 67 000 7267

09 67 000 7268

09 67 000 7266

10 000 pieces/reel  
 Unrolling left  
 Unrolling left reversed  
 Unrolling right reversed

09 67 000 7257  
 09 67 000 7247  
 09 67 000 7237

09 67 000 7258  
 09 67 000 7248  
 09 67 000 7238

09 67 000 7256  
 09 67 000 7246  
 09 67 000 7236

Individual contacts

AWG 24-20  
 0.25-0.56  
 stranded

09 67 000 8277<sup>1)</sup>

09 67 000 8278<sup>1)</sup>

09 67 000 8276<sup>1)</sup>

500 pieces/reel  
 Unrolling left

09 67 000 8267

09 67 000 8268

09 67 000 8266


10 000 pieces/reel  
 Unrolling left  
 Unrolling left reversed  
 Unrolling right reversed

09 67 000 8257  
 09 67 000 8247  
 09 67 000 8237

09 67 000 8258  
 09 67 000 8248  
 09 67 000 8238

09 67 000 8256  
 09 67 000 8246  
 09 67 000 8236

Unrolling direction



500 pieces/reel  
 Unrolling left

10 000 pieces/reel  
 Unrolling left

10 000 pieces/reel  
 Unrolling left reversed

10 000 pieces/reel  
 Unrolling right reversed

for HARTING tools

<sup>1)</sup> Minimum order 500 pieces or multiples of 500  
 Insertion and removal tool see chapter 20  
 Contact dimensions see page 05.31