

## Revolving centring points

With extended 60°/60° moving point

**ATORN**<sup>®</sup>

### Application

Perfect all-purpose point for universal use on manual lathes. Particularly suitable for copy turning. The extended moving point makes it easy to move the lathe tool up to the flat side of the workpiece.

### Version

- Tool fully hardened and polished
- Bearings positioned to accommodate high axial forces
- Concentricity tolerance max. 0.005 mm

### Advantage

- Radial shaft seal prevents the ingress of dirt and coolant



<b>Art. No.</b>	<b>22134 020</b>
<b>Morse taper size</b>	MK 3
<b>Programming size</b>	54 mm
<b>Programming size for housing</b>	68.5 mm
<b>Max. workpiece weight</b>	170 kg
<b>Max. rotation speed</b>	4200 U/min(rpm)
<b>Concentricity tolerance</b>	0.005 mm
<b>Diameter of housing</b>	54 mm
<b>Tip diameter</b>	13 mm

### EAN-Code

4050293272499