

System trolley CONNECT Model 354

Desk, hanging cabinet and perforated metal plate wall



Execution:

- Mobile base trolley, consisting of 2 sectional supports and pushing handle
- Tray base single-sided—depth 450 mm
- Assembly of the attachment elements possible without tools in the 50 mm grid
- 1 x perforated metal plate wall, width x height 720 x 600 mm, with 10 x 10 mm square holes and 38 mm axis distance
- 1 x plastic-coated worktop, width x depth x height 830/1000 x 500 x 28 mm
- 1 x suspended cabinet with hinged doors, lockable, width x depth x height 760 x 330 x 450 mm
- Incl. 4 steering rollers (diameter 125 mm), 2 of which have locking devices
- Delivery: ready mounted, rollers unmounted

Delivery:

Ready mounted, rollers unmounted.



| | |
|---|------------------|
| Art. no. | 50240 611 |
| Brand | ANKE |
| Manufacturer Part Number | 962.084 |
| Model | CVM 354 |
| Width | 800 mm |
| Depth | 450 mm |
| Height | 1950 mm |
| Design | One side |
| Load-carrying capacity | 200 kg |
| Load-carrying capacity of storage area | 30 kg |
| Load-carrying capacity of base plate | 100 kg |
| Distance between centre of hole and centre of hole | 38 mm |
| Number of steering rollers | 4 PCS |
| Wheel diameter | 125 mm |
| With wheel lock | Yes |
| With sliding handle | Yes |
| Material | Sheet steel |
| Colour of trolley | Optional |
| Colour of perforated panel | Optional |
| Colour of front | Optional |
| Surface | Powder-coated |
| Gross Weight | 75.956 kg |
| Product Group | 502 |

EAN

4014641067175