

Workbench trolleys

Working height 840 mm, with 4 drawers and 1 door

Application:

The mobile workstation with versatile options for use.

Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick
- Suitable insert material for drawers, see from no. 50485 060-265 and from no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Advantage:

- When you buy this product, you plant a tree and also receive a tree certificate!
- When you buy this product, you plant a tree and also receive a tree certificate!



| | |
|--|--|
| Art. no. | 50286 234 |
| Brand | HK |
| Manufacturer Part Number | 50286234 |
| Number of fixed rollers | 2 PCS |
| Working height | 840 mm |
| Number of steering rollers | 2 PCS |
| Worktop width | 1155 mm |
| Number of drawers | 4 PCS |
| Worktop height | 40 mm |
| Number of doors | 1 PCS |
| Worktop depth | 700 mm |
| Pullout type | Full extension |
| On castors | Yes |
| Moving device, can be lowered | No |
| Colour of front | Anthracite grey RAL 7016 |
| Cabinet colour | Light grey RAL 7035 |
| With single pull-out safety brake | Yes |
| Surface | Powder-coated |
| With wheel lock | Yes |
| Load-carrying capacity | 820 kg |
| Wheel diameter | 200 mm |
| Type | mobile |
| Lock type | DOM® locking system |
| Material of worktop | Solid beech |
| Drawer front height | 1 x 60 mm, 1 x 90 mm, 1 x 150 mm, 1 x 180 mm |
| Material | Sheet steel |
| Drawer width (inner dimension) | 450 mm |
| Drawer width (inner dimension) x drawer depth (inner dimension) | 450 x 600 mm |
| Drawer depth (inner dimension) | 600 mm |
| Load-carrying capacity per drawer | 70 kg |
| Material of wheel | Solid rubber |
| Central locking | Yes |
| Gross Weight | 130.000 kg |
| Product Group | 501 |

EAN

4053625403370