

WEF 15-125 Quick flat head angle grinder

1550 W

metabo[®]

Application:

Specially developed for removing weld slag, rust or paint in narrow frame constructions and for working in tight spaces

Execution:

- Metabo S-automatic mechanical safety clutch
- cut-out carbon brushes for protecting the motor
- electronic safety cut-off: reduces kick-back if the disc is blocked
- Smallest achievable angle: 43°

Delivery:

protective cover, support flange, M-Quick clamping nut, additional handle, Flexiamant Super Convex lamellar grinding disc (125 mm; P60), Flexiamant Super FKS 60 rough grinding disc



Art. no.	70373 810
Brand	METABO
Manufacturer Part Number	613082000
Model	WEF 15-125 Quick
Manufacturer Article Number	613082000
Battery included	No
Number of rechargeable batteries/batteries	0
Washer diameter	125 mm
Power input	1550 W
Power output	940 W
Idle speed	11000 rpm
Thread dimension of spindle	M14
Weight	2.7 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With electronic feedback	Yes
With reverse switch off	Yes
With disc brake	No
With quick clamping system	Yes
With dead man function	No
Gross Weight	4.120 kg
Product Group	745

EAN

4007430275707