

Pneumatic angle drill MD-3312B


Angled version



Version:

- Anti-clockwise and clockwise rotation
- Noise-dampened air outlet with handle

Art. no.	75066 106
Model	MD-3312B
Max. drilling diameter in steel	10 mm
Max. idle speed	1900 rpm
Power rating	380 W
Air consumption	6 l/s
Min./max. drill chuck span width	1-10 mm
Inner hose diameter	6.5 mm
Weight	0.91 kg
With right/left-hand rotation	Yes
Operating pressure	6.3 bar
Length	205 mm
Sound-pressure level	77 dB



EAN-Code

8717981000111