




Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------


Fibre optic cable, double ended, multi mode, metal, 50 µm
2 x Han® 3 A, 2 x LC duplex

Length: a = 1 m	33 54 211 0010 002
a = 5 m	33 54 211 0050 002
a = 10 m	33 54 211 0100 002
a = 20 m	33 54 211 0200 002
a = 40 m	33 54 211 0400 002
a = 50 m	33 54 211 0500 002
a = 100 m	33 54 211 1000 002

double ended



a = length



Protection level: IP65/IP67

Fibre optic breakout cable, multi mode, 50 µm

Length: 10 m	33 54 751 0100 002
Length: 20 m	33 54 751 0200 002
Length: 100 m	33 54 751 1000 002



FRNC jacket
4-fibre multi mode 50 µm
Outer diameter: 7.9 mm
Min. bending radius:
Installation: 9.8 cm
Operating: 7.9 cm