

Crimpeinsätze für unisolierte Verbinder nach DIN 46234 / 46235 / 46267



Art. Nr. 624 000 3 + 624 031 3 0



Art. Nr.	EAN 4049002	Kapazität	Profil	Verbinder	Abbildung	Anwendungsbereich				
						PEW 12	E-PEW 12	CM 25-1	CM 25-5	CM 25-6
624 020 3 0	014048	0,25–0,75 mm ² 1,0–1,5 mm ² 2,5 mm ²				•	•	•	•	•
624 030 3 0	014079	4,0 mm ² 6,0 mm ² 10,0 mm ²				•	•	•	•	•
624 031 3 0	014109	1,5 mm ² 2,5 mm ² 4,0 mm ² 6,0 mm ² * 10,0 mm ² **				•	•	•	•	•
624 032 3 0	014451	0,5–1,0 mm ² 1,5–2,5 mm ² 4,0–6,0 mm ² 10,0 mm ²				•	•	•	•	•
624 033 3 0	026683	16,0 mm ² 25,0 mm ²				•	•	•	•	•
624 036 3 0	125003	0,1–0,5 mm ² unisoliert 0,1–0,5 mm ² isoliert				•	•	•	•	•
624 1071 3 0	111075	0,5–1,5 mm ² 1,5–2,5 mm ² 4,0–6,0 mm ² * 6,0–10,0 mm ² **				•	•	•	•	•

* nach DIN 46267

Crimpeinsätze für Flachstecker


· nach ehemaliger DIN 46 247, 46 345, 46 346



Art. Nr. 624 000 3 + 624 745 3 0



Art. Nr. 624 000 3 + 624 050 3 01



Art. Nr.	EAN 4049002	Kapazität	Profil	Verbinder	Abbildung	Anwendungsbereich				
						PEW 12	E-PEW 12	CM 25-1	CM 25-5	CM 25-6
624 045 3 01	132292	0,1–0,25 mm ² 0,5–1,0 mm ² 0,5–1,0 mm ² 1,5–2,5 mm ² mit Kontaktaufnahme, Steckerbreite 2,8 + 4,8 mm				•	•	•	•	•
624 050 3 01	114427	0,5–1,0 mm ² 1,5–2,5 mm ² 4,0–6,0 mm ² mit Kontaktaufnahme, Steckerbreite 4,8 + 6,3 mm				•	•	•	•	•
624 742 3 0	019197	0,5–1,0 mm ² 0,5–1,0 mm ² 1,25–2,5 mm ²				•	•	•	•	•
624 742-1 3 0	143939	0,5–1,0 mm ² 0,5–1,0 mm ² 1,25–2,5 mm ²				•	•	•	•	•
624 745 3 0	019203	1,25–2,5 mm ² 3,0–4,0 mm ² 4,0–6,0 mm ²				•	•	•	•	•
624 745-1 3 0	098109	1,25–2,5 mm ² 3,0–4,0 mm ² 4,0–6,0 mm ²				•	•	•	•	•