


13	742300	Hexagon socket head cap screw ISO 4762-M4x16	4	3	-	2,2
12	9400029901	Han HPR HPTC coding-element	2			
11	9110026214	Han HPR HPTC 400-fe.-cont.-120mm ²	1			
10	19400020410_03	Han HPR HPTC 400 CS-HB-c.-retainer	1			
9	19400020410_02	Han HPR HPTC 400 CS-cover-insul.-body	1			
8	19400020410_01	Han HPR HPTC 400 CS-HB-insul.-body	1			
7	19400020400_11	Han HPR HPTC 400 CS-Cover	1			
6	19000007124	Han CGM-M-Rail M32 D16-20.5mm	1	36	40	20,0
5	19400020490_05	O-Ring	1			
4	19400020490_06	O-Ring	2			
3	743200	Lock Washer	2			
2	742700	Hexagon socket head cap screw ISO 4762-M6x35	2	5	-	6,0
1	19400020407_50	Han HPR HPTC 400 CS-HB-M32	1			
item	partnumber	partname	QTY	SW1	SW2	tightening torque Nm

parts in scope of delivery are not assembled
 assembly instruction enclosed
 crimp zone acc. to DIN EN 46235, indicator 20
 for stranded fine wire acc to VDE 0295 class 5/ IEC 60228 class 5
 wire gauge: 120mm²



Coating	A=	mm ²	V=	mm ³	m=	g	Mat.
	All Dimensions in mm Original Size DIN A3	Scale 1:2	Free size tol.	Ref.			
				Sub.			
	All rights reserved Department EL PD	Created by MEYERLE	Inspected by 00103912	Standardisation	Date 2021-10-01	State Final Release	
HARTING D-32339 Espelkamp		Title Han HPR HPTC 400 CS UNSH IP65/67 120		Doc-Key / ECM-Nr. 100931981/UGD/002/F 500000203536		Rev. F	Page 1/1
Type	TB	Number	10 40 271 2136				