


## ADAPTOR M12 MALE 5 POLE/ M12 FEMALE 4 POLE SHIELDED

For analog sensors

Adapter  
M12 - M12  
Male straight to female straight  
5-pole, shielded

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Form

42261

#### Technical Data

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Compression gland	Zinc die casting, matte nickel plated
Protection	IP67 inserted and tightened (EN 60529)
Material	PUR

#### General data

Temperature range	-25...+85 °C
-------------------	--------------

Test isolation voltage	0.8 kVrms
------------------------	-----------

**Commercial data**

country of origin	DE
-------------------	----

customs tariff number	85369010
-----------------------	----------

minimum order quantity	1
------------------------	---