



Datenblatt - Fiche technique - Data sheet

**21.15.0875**





ROLINE S/FTP-(PiMF-)Patchkabel Kat.6a, Massivdraht, grau, 90,0 m

Cordon ROLINE Cat.6a S/FTP (PiMF) solide, gris, 90,0 m


ROLINE S/FTP Patch Cord Cat.6a, solid, grey, 90.0 m

1 2 3 4 5 6

length (see below table list)



Print: roline S/FTP INSTALL CABLE 23AWG 4PR ANSI/TIA 568C.2 CAT.6A XXXXXX-X XXXXM



**Specification :**

**Material :**

1. RJ45 Plug : for 23AWG Solid wire.
  - 1-1. Housing : Polycarbonate, UL 94V-2, Blue color.
  - 1-2. Contact finished : Min. 50 micro-inch Gold plating over min. 50 micro-inch Nickel plating on surface contact area.
  - 1-3. Contact material : Phosphor Bronze.
  - 1-4. Shield : Zinc Alloy with Nickel plated.
2. SR : PC 2250 UL 94V-2.
3. Cable :
  - 3-1. Jacket : PVC.
  - 3-2. Conductor : 23 AWG Solid copper.
  - 3-3. Isolation : Foam PE.
  - 3-4. Shield : Aluminum Foil.
  - 3-5. Cable structure : S/FTP, 4 twisted pair.

21.15.0870	20m	grey
21.15.0871	30m	grey
21.15.0872	50m	grey
21.15.0873	70m	grey
21.15.0875	90m	grey

**Remark :**

- (1) Jacket Color  
Gray(RAL7035)
- (2) Wiring  
T568B
- (3) Length (as shown on the table list)
- (4) Length Unit : meter

No.	MODIFIED AREA	ORIGINAL	MODIFY	DATE	MODIFIER
1					

*# : Matching DIM.	DRAWING	08.AUG.2013	<b>rotronic</b>		
** : Important DIM.	CHECK	08.AUG.2013			
Others General DIM.	APPROVAL	08.AUG.2013			
GENERAL TOLERANCE OF DIMENSIONS		ITEM NO.	21.15.0870, 21.15.0871, 21.15.0872, 21.15.0873, 21.15.0875		
X.XXX ±0.005	X.XX ±0.05	SCALE	1/1 (A4)	DESC.	ROLINE Cat. 6a S/FTP Patch Cord, solid, grey
X.X ±0.1		UNIT		mm	
DRAWING CLASSIFICATION			S	SHEET	1 OF 1

1 2 3 4 5 6 10cm