





328-522

LAMP DATA

T-3¼ Miniature continued									
Volts	Amps/ Watts	Lumens	MSCP	Life (hours)	Filament shape	T-3¼ 10x28mm Miniature Screw E10 (MES)	T-3¼ 10x30mm Miniature Screw E10 (MES)	T-3¼ 10x28mm Miniature Bayonet BA9s (MCC)	T-3¼ 10x30mm Miniature Bayonet BA9s (MCC)
24	1.2W	4.0	0.32	5,000	C-2F	W592		W568	
24	2W	6.3	0.50	10,000	C-2F	W1252		W1201	
24	0.12	12.0	0.95	3,000	C-2F	W599		W600	
28	0.04	4.3	0.34	3,000	C-2F				1819
28	0.07	12.6	1.00	1,000	C-2F				1829
24-28	2W	4.5	0.36	25,000	C-2F	W1122		W1152	
28	0.08	7.8	0.62	7,500	C-2F				757
28	0.10	20.0	1.60	1,000	C-2F	W601			1820
28	0.17	38.0	3.00	1,500	C-2F				1864
28	0.17	44.0	3.50	500	C-2F				313
30	2W	6.3	0.50	10,000	C-2F	W1214		W1204	
36	2W	6.3	0.50	10,000	C-2F			W1205	
48	0.02	1.9	0.15	3,000	CC-2F			W1166	
48	2W	6.3	0.50	5,000	CC-2F			W1206	
48	0.10	41.5	3.30	1,000	CC-2F		1823		
50	0.05	9.0	0.72	5,000	CC-2F	W607		W608	
55	0.05	13.8	1.10	5,000	CC-2F				1835
60	2W	5.0	0.40	3,000	CC-2F	W1257		W1207	
60	3W	10.5	0.84	3,000	CC-2F	W609		W610	
60	0.06	15.0	1.19	1,000	CC-2F	60S1		60B1	
130	0.02	3.0	0.24	3,000	CC-4F	W1159		W1121	
130	0.02	3.8	0.30	5,000	2xCC-2F			W1121T	
NOTES All dimensions in mm. Drawings not to scale This sheet lists a selection of available lamps See previous page for lower voltages Please enquire for other ratings and sizes Special options: Aged and selected, Colour coated bulbs Silicone rubber filters									