

Pneum. contact metal ID 3 male



Part number	09 14 000 6303
Specification	Pneum. contact metal ID 3 male
HARTING eCatalogue	https://b2b.harting.com/09140006303

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight
Features	The Han® Pneumatic contacts without shut-off are suitable for the use inside a vacuum. (Limit: 100 mbar = 100 hPa \approx approx 90% vacuum)

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 +85 °C
Operating pressure	≤10 bar
Tube inner diameter	3 mm

Material properties

Material (contacts)	Brass
Material (seal)	HNBR (hydrated NBR)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained

Product data sheet 09 14 000 6303 Pneum. contact metal ID 3 male



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
OL / CSA	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size 10
Net weight 11.75 g
Country of origin Romania
European customs tariff number 39269097
GTIN 5713140189270
ETIM EC000796
eCl@ss 27440204 Contact for industrial connectors