

## TOLEDO BALL

ToLEDo BALL V6 470LM 827 E14 SL

0026954



### Product features

- Compact and elegant design
- Suitable replacement for halogen, incandescent and compact fluorescent ball lamps
- Instant light at the flick of a switch
- Uniform light distribution
- Good colour rendering (CRI 80)
- Perfect for hotels, restaurants, lobbies, corridors, stairwells, reception areas
- Lower maintenance costs
- A+ energy rating



## PRODUCT OVERVIEW

Product name	ToLEDo BALL V6 470LM 827 E14 SL
Technology	LED
Watt (Rated) (W)	5
Type	TOLEDO BALL
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740489
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Beam Angle (°)	150
Wattage (W)	5
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288269542

## DATA TABLE

### General data

Product name	ToLEDo BALL V6 470LM 827 E14 SL
Technology	LED
Watt (Rated) (W)	5
Type	TOLEDO BALL
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959

## TOLEDO BALL

ToLEDo BALL V6 470LM 827 E14 SL

0026954

E-number FI	4740489
Warranty	3 years

### Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Beam Angle (°)	150
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	5
Equivalent watt (W)	40
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	>50000
Inrush Current (A)	3
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	138
Max. Luminaires per 16A C Breaker	222
Max. Luminaires per 20A C Breaker	278

### Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

### Physical data

Nominal Product Length (mm)	82
Nominal Product Diameter (mm)	45
Weight (kg)	0.05

### Packaging

Single packaging type	Carton
Product EAN number	5410288269542
Packaging single length / height (cm)	10.2
Packaging single width (cm)	4.9
Packaging single depth (cm)	4.9
DUN14 (inner)	25410288269546
Units per inner package	6
Packaging inner length / height (cm)	15.3
Packaging inner width (cm)	12.7
Packaging inner depth (cm)	10.6
DUN14 (outer)	15410288269549

## TOLEDO BALL

*ToLEDo BALL V6 470LM 827 E14 SL*

0026954

Units per outer package	60
Packaging outer length / height (cm)	55.3
Packaging outer width (cm)	15.1
Packaging outer depth (cm)	33.6

### Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures