

Flap bottom container

Carrying capacity of 1000–1500 kg, without wheels

Execution:

- Robust steel sheet structure with smooth inside walls
- Releasing the trapdoor per cable pull from the fork-lift truck seat
- Rubber cushioning to lessen the impact when the trap door is opened
- The trapdoor closes by itself when pushed
- Protection against accidental slipping and opening of trap door
- Mounts for lift truck and crane
- 100 mm ground clearance—transportable with a pallet truck
- With 4 crane lugs diameter 40 mm, can be triple stacked on top of each other (only on version without wheels)

Delivery:

Goods supplied without packaging as standard.
Packaging available for an additional charge.



Art. no.	50266 704
Volume	2 m ³
Length x width x height	1040 x 1845 x 1445 mm
Distance between brackets	615 mm
Fork guide width	185 mm
Fork guide height	75 mm
With stacker seat release of floor flap	Yes
Load-carrying capacity	1500 kg
Colour	Light blue RAL 5012
Surface	Lacquered
Gross Weight	232.000 kg
Product Group	5AI

EAN

4052462007390