

Flat magnetic grips, hard ferrite core, steel jacket

With threaded stem


ORION[®]

Application:

Auxiliary materials with universal application during clamping, assembling, lifting and welding operations, and for installing in devices etc.

Version:

- With hard ferrite core
- Surface galvanised
- Magnetic shielding
- With threaded stem
- Operating temperature up to 100°C



Art. no.	51144 620
Outer diameter	32 mm
Height	22 mm
Thread dimension	M5
Adherence strength	80 N

EAN-Code

4039247261789