

Electronics side cutters without bevel, with wire clamp

Black phosphated surface

ATORN®

Version

- C-60 steel, blade hardness from 63-65 HRC
- Inductively hardened blades
- Largest cuttable diameter (copper): 0.2-2 mm

Advantage

- Anti-glare, phosphatised surface enables safe working
- With low-friction double-opening spring and two-component handles for fatigue-free, ergonomic working



Art. No.	53027 130
Length	112 mm
Max. soft wire diameter cutting capacity	1.3 mm
Head design	Wire clamp
Surface	Phosphated
Material of the grip handle	2-component plastic

EAN-Code

4050293170528