

Pneumatic blow-out and liquid gun, series 208

Star tip with removable tube



Application:

For cleaning work using compressed air, coolant or non-explosive water-based liquids.

Execution:

- Nozzle made of brass
- With infinite flow control

Advantage:

- Ergonomic handle piece for working comfortably
- Satisfies OSHA and ArbStättV (German workplaces ordinance) requirements
- High blowing force
- Infinitely adjustable air flow



Art. no.	75179 006
Brand	CEJN
Manufacturer Part Number	112083200
Model	Star-Tip, low-noise, removable pipe
Max. operating pressure	16 bar
Burst pressure	64 bar
Connection thread	R 1/4 inch
Sound-pressure level	79 dB
Min./max. temperature conditions	-20 to +60 °C
Weight	0.096 kg
Gross Weight	0.121 kg
Product Group	7AI

EAN

739139020609 1