

DULUX T PLUS 26 W/830

OSRAM DULUX T PLUS | CFLni, 3 tubes, with 2-pin base for CCG operation



Areas of application

- Offices, public buildings
- Shops
- Supermarkets and department stores
- Hotels, restaurants
- Industrial lighting

Product benefits

- Very economical
- Good quality of light
- Excellent luminous flux
- Long service life
- Improved maintenance

Product features

- Average life: 10,000 h
- Color rendering index R_a: 80...89
- Short and compact pin-base lamp with triple-turn tubes
- Single-ended two-pin plug-in GX24d base



Technical data


Electrical data


Nominal wattage	26.50 W
Rated wattage	26.50 W


Photometrical data

Nominal luminous flux	1800 lm	
Rated luminous flux	1800 lm	
Color temperature	3000 K	
Light color	830	
Light color as per EN 12464-1	LUMILUX Warm White	
Color rendering index Ra	8089	
Luminous flux at 25 °C	1800 lm	
Rated LLMF at 4,000 h	0.80	
Rated LLMF at 6,000 h	0.77	
Rated LLMF at 8,000 h	0.75	
Luminance	6 cd/cm ²	
Color rendering group	18	

Dimensions & weight







Overall length	139.0 mm	
Product weight	63.00 g	
Tube diameter	12 mm	
Length	139.0 mm	
Length acc. to IEC standard	130 mm	
Length with base excl. base pins/connection	116.00 mm	

Temperatures

Lifespan

Nominal lamp life time	10000 h	
Rated lamp life time	10000 h	
Service life	6500 h	
Rated lamp survival factor at 2,000 h	0.99	
Rated lamp survival factor at 4,000 h	0.99	
Rated lamp survival factor at 6,000 h	0.95	
Rated lamp survival factor at 8,000 h	0.81	
Operation mode LLMF/LSF	50 Hz	
Lifespan	10000 h ¹⁾	

1) With CCG/LLCG

Additional product data

Base (standard designation)	GX24d-3
Lamp mercury content	1.9 mg
Appropriate disposal acc. to WEEE	Yes

Capabilities

Suitable for indoor	Yes
---------------------	-----


Certificates & standards

Energy efficiency class	В
Energy consumption	32 kWh/1000h

Country specific categorizations

ILCOS FSM-26/830-I-GX24d-3

Light Distribution




Spectral power distribution

Equipment / Accessories

- Suitable for operation on conventional control gear
- Suitable for 0.22 A control gear only (DULUX T 18 W PLUS)

Safety advice

In case of lamp breakage: www.osram.com/brokenlamp



Circuit diagram

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300342061	DULUX T PLUS 26 W/830	Shipping carton box 10	228 mm x 161 mm x 128 mm	4.70 dm ³	874.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.