


**1/2"-20-Round-Plug Connector, Double-Ended Cordsets, Automotive Color Code**


RST...U-RKT ...U | RST...U-RKWT...U



**3, 4-, and 5-Poles**


1/2"-20 actuator/sensor cordsets, double-ended, 3-, 4- and 5-Poles, male to female straight connector, dual keyway, 18 and 22 gauge, Automotive color code.

**RST...U-RKT...U**



1/2"-20 actuator/sensor cordsets, double-ended, 3-, 4- and 5-Poles, male to female 90° connector, dual keyway, 18 and 22 gauge, Automotive color code.


**RST...U-RKWT...U**



**Pin Assignments**


1/2"-20 - Male / Female

**3 poles**




1 = green  
2 = red/black  
3 = red/white

**4 poles**




1 = red/black  
2 = red/white  
3 = red  
4 = green

**5 poles**



1 = red/white tr.  
2 = red  
3 = green  
4 = red/yel tr.  
5 = red/blk tr.



# Be Certain with Belden

## 1/2"-20-Round-Plug Connector, Single-Ended Cordsets, Automotive Color Code RST...U-RKT...U | RST...U-RKWT...U

### Technical Data

#### Environmental

Degree of protection IP 67 / NEMA 6P  
Operating temperature range -40°C (-40°F) / +90°C (+194°F)

#### Mechanical

Housing / Molded body TPU, yellow  
Insert TPU, yellow  
Contact CuZn, gold over nickel plated  
Coupling nut CuZn, nickel-plated

#### Electrical

Current rating 4 A  
Voltage rating 250 V

### Cable Specifications - Automotive Color Code

Cable No.	Outer Jacket	Gauge	Conductor Size	Jacket Color	OD
688	PVC	18AWG	3 x 0.75mm <sup>2</sup>	Yellow	.290" (7.4 mm)
689	PVC	18AWG	4 x 0.75mm <sup>2</sup>	Yellow	.290" (7.4 mm)
755	TPE	18AWG	5 x 0.75mm <sup>2</sup>	Yellow	.333" (8.5 mm)
618	PVC	22AWG	3 x 0.34mm <sup>2</sup>	Yellow	.180" (4.6 mm)
674	PVC	22AWG	4 x 0.34mm <sup>2</sup>	Yellow	.190" (4.8 mm)
673	PVC	22AWG	5 x 0.34mm <sup>2</sup>	Yellow	.210" (5.3 mm)
664	PUR	22AWG	3 x 0.34mm <sup>2</sup>	Yellow	.190" (4.8 mm)

Part Number	Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RST 3U-RKT 3U-688/...F    RST 3U-RKWT 3U-688/...F	3	PVC	3 F / 6 F / 12 F / 15 F	
RST 4U-RKT 4U-689/...F    RST 4U-RKWT 4U-689/...F	4	PVC	3 F / 6 F / 12 F / 15 F	
RST 5U-RKT 5U-755/...F    RST 5U-RKWT 5U-755/...F	5	TPE	3 F / 6 F / 12 F / 15 F	
RST 3U-RKT 3U-618/...F    RST 3U-RKWT 3U-618/...F	3	PVC	3 F / 6 F / 12 F / 15 F	
RST 4U-RKT 4U-674/...F    RST 4U-RKWT 4U-674/...F	4	PVC	3 F / 6 F / 12 F / 15 F	
RST 5U-RKT 5U-673/...F    RST 5U-RKWT 5U-673/...F	5	PVC	3 F / 6 F / 12 F / 15 F	
RST 3U-RKT 3U-664/...F    RST 3U-RKWT 3U-664/...F	3	PUR	3 F / 6 F / 12 F / 15 F	