

RF TERMINATION

Type 65_MCX-50-0-4/111_N

Description

Standard Termination, Low Power



Product Configuration

Connector	MCX plug (male)
Interface standards	IEC 60169-36_CECC 22220

Technical Data

Electrical Data

Nominal Impedance	50 Ω
Frequency range	0 to 6 GHz
VSWR max.	1.22
Power rating	1 Watt average power up to 85 °C ambient temperature, linearly derated to 0 Watt at 115 °C ambient temperature.

Mechanical Data

Weight	0.001 kg
--------	----------

Environmental Data

Operating temperature	-40 °C to 115 °C
Water and dust resistance 2011/65/EC (RoHS)	No (according to IEC 60529, data refer to the coupled state) compliant

Material Data

Piece Part	Material	Surface Plating
Centre contact	Brass	Gold Plating
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00177690
-----------------	--------------

Ordering Information

Single Packaging Packaging	65_MCX-50-0-4/111_NE
-------------------------------	----------------------