

Han 10B-HBM-Rear Fit-SL



Part number	09 30 010 0397
Specification	Han 10B-HBM-Rear Fit-SL
HARTING eCatalogue	https://b2b.harting.com/09300100397

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting
Туре	Low construction
Version	
Size	10 B
Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Field of application	Standard hoods/housings for industrial connectors
Pack contents	Mounting frame is included within the delivery

Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated

Page 1 / 2 | Creation date 2023-01-12 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Material properties

Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0

Specifications and approvals

Approvals	DNV GL
CE	Yes
Commercial data	
Packaging size	1
Net weight	127.2 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140164604
eCl@ss	27440202 Shell for industrial connectors