


MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it

## Technical Datasheet

  
**tasker® C100 – 2x0,35 mm<sup>2</sup>**  
**Flat Audio Divisible Cable**



A

B

**CATEGORY**    **Polarized Flat Cable** (See Audio Catalogue)

- A:**        Soft **PVC** Sheath, available in different colors.  
 Outer cable dimension 1,90 x 3,90 mm (±0,20) mm.
- B:**        One conductor made of O.F.C. tinned copper and one of O.F.C. Red  
 Copper. Formation with 0,20 mm wires.  
 Nominal cross section 2x0,35 mm<sup>2</sup>.

**CUSTOM**        This product is also available in **L.S.Z.H., PE, PUR.**

### Conductors Properties

<b>Conductor Resistance</b>	60 Ω/Km ± 5%
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	X	Indoor	Interno Edificio	<b>INSTALLATION</b>	X	Fixed	Fissa	<b>INFORMATION</b>	X	RoHS2 Compliant
<b>Impiego</b>	X	Outdoor Limited	Esterno Limitato	<b>Posa</b>	X	Flexible Limited	Flessibilità limitata	<b>Informazioni</b>	X	Ver.C / 16.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			