



Sample photo

**Order symbol:** AR181610CHSSL  
**Product nbr:** 8561070  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque cover w/S.S.  
 Lockable latch

**EAN:** 6418074066855  
**EI. number:**  
**Finland:**

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height	Accessories:	
mm:	457	406	254	ALBP1816	Aluminum Back Panel
inch:	18.0	16.0	10.0	ADFP1816	Dead Front Panel w/ screws
<b>Materials:</b>				ASP1816	Aluminum Swing Panel
<b>Material:</b>	Polycarbonate			APSPK1816 Plastic	Swing Panel Kit incl. Panel
<b>Base colour:</b>	RAL 7035 -light grey			ASPK1816	Swing Panel Kit incl. Panel
<b>Cover screws material:</b>	Stainless steel			AMFL16	16" Mounting Flange Set
<b>Cover colour:</b>	RAL 7035 -light grey			<b>Rating:</b>	
<b>Gasket material:</b>	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
<b>Temperatures:</b>				Electrical insulation: Totally insulated	
<b>Temperature °C (short term):</b>	-40 ... 140 °C			Halogen free (DIN/VDE 0472, Part 815): 0	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			UV resistance: UL 508	
<b>Temperature °F (short term):</b>	-40 ... 284 °F			Flammability Rating: UL 508	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Accessories:</b>				NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13	
ABP1816	Painted Steel Back Panel				

