

## Product information

# 95 16 160

## KNIPEX StepCut

### Cable Shears

IEC 60900 DIN EN 60900



- Small, light, strong: comfortable cutting without crushing and just 160 mm in size
- Noticeably less effort: the gradations cut wires one after the other; cutting is up to 40% easier than with standard cable shears of the same length!
- Ergonomic handle design: optimal cutting feel even for larger cable diameters
- Cuts multi-core stranded copper and aluminium cables up to Ø 15 mm (50 mm<sup>2</sup>)
- Cuts solid copper and aluminium cables up to 5 x 4 mm<sup>2</sup>
- Cuts without crushing
- Bolted joint: precise, effortless, durable
- Pinch guard fitted for safe work
- Not suitable for steel wire and hard drawn copper conductors
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 56 HRC
- High-grade special tool steel, forged, oil-hardened

 1000 V



### General

Article No.	95 16 160
EAN	4003773085966
Shears	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	225 g
Dimensions	160 x 60 x 28 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacity copper cable, multiple-stranded	50 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0
VDE tested	yes

*technical change and errors excepted*



